



RoHS&REACH

ECN NO.	DESCRIPTION	DATE
A-0		2022.3.19



NOTES:


MATERIAL:

- HOUSING MATERIAL :ABS
- CONTACT MATERIAL :ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE;
GOLD PLATING OVER NICKEL
- WIRES :UL 1061 26#

ELECTRICAL/PHYSICAL:

- VOLTAGE RATING :125 VAC RMS
- CURRENT RATING :1.5 AMP
- CONTACT RESISTANCE :30 MILLIOHMS MAX
- INSULATION RESISTANCE :500 MEGOHMS MIN @500V DC
- DIELECTRIC WITHSTANDING RESISTANCE :1000V AC RMS 60Hz. 1MIN
- DURABILITY :750 CYCLES MIN
- TEMPERATURE :-40°C/+85°C

PH2.0



623K - X X X X X L:Wire Length

No. Of Positions	No. Of Contacts	Wire Style	Color	Gold Plating
4, 6 or 8	2, 4, 6 or 8	1-24 AWG 2-26 AWG 3-28 AWG	1-Black 2-Gray 3-Other	1-1u" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"

6	UL 1061 26AWG Wire	2*50mm
5	Contact (Fu*)	2pcs
4	PH-T	2pcs
3	Terminal	2pcs
2	PH2.0-2Y (PA66 White)	1pcs
1	623K (ABS Gray)	1pcs
NO.	Specification	Quantity

Sequence	Color	Color
2	Green	Green
1	Red	Red
	623K	PH2.0

尺寸标注	公差		设计	X.C.S	比例	1:1
	长度	角度				
.X	±0.25	±2.0°	设计		单位	mm
.X	±0.20	±1.5°	审核		图幅	A4
.XX	±0.15	±1.0°	批准		版本	A-0
.XXX	±0.10	±0.5°	角法	⊕	图数	第1页 共1页

恒连电子科技有限公司
EVERCOM ELECTRONIC TECHNOLOGY CO., LTD
<http://www.chinarj45.com>

产品型号: 623K 6P2C灰色 TO PH2.0白色 L50 FU
产品编号: _____ 图纸编号: _____

1

2

3

4

5

6