


RoHS Compliant




NOTES:

MATERIAL:

- 1. HOUSING MATERIAL :ABS(UL 94V-0)
- 2. CONTACT MATERIAL :ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE;  
GOLD PLATING OVER NICKEL
- 3. WIRES :UL 1061 26#

ELECTRICAL/PHYSICAL:

- 1. VOLTAGE RATING :125 VAC RMS
- 2. CURRENT RATING :1.5 AMP
- 3. CONTACT RESISTANCE :30 MILLIOHMS MAX2
- 4. INSULATION RESISTANCE :500 MEGOHMS MIN @500V DC
- 5. DIELECTRIC WITHSTANDING RISTANCE :1000V AC RMS 60Hz. 1MIN
- 6. DURABILITY :750 CYCLES MIN
- 7. TEMPERATURE :-40° C/+85° C

|                      |                        |                                   |            |                                       |                                     |                |  |
|----------------------|------------------------|-----------------------------------|------------|---------------------------------------|-------------------------------------|----------------|--|
| JACK WITH FLITER     | NOT SCALED DRAWING     | TOLERANCE UNLESS OTHERWISE NOTICE | INCH       | MM                                    | DR. Nina                            | DATE MAY-22-20 |  <b>恒连电子科技有限公司</b><br>HENGLIAN ELECTRONIC TECHNOLOGY CO.,LTD<br><a href="http://www.chinarj45.com">http://www.chinarj45.com</a> |
|                      | THIRD ANGLE PROJECTION | LINEAR                            | MM<br>INCH | .00±0.01<br>.000±0.005<br>.0000±0.002 | .00±0.25<br>.000±0.13<br>.0000±0.05 | CK'D Jack      |  |
| DWG. NO. HL012052115 | MM<br>INCH             | ANGLE+0° 30'                      | RADIL      | +0.45<br>-0.15                        | APP'D Jack                          | MAY-22-20      |  |