



SPECIFICATIONS:

- ELECTRICAL CHARACTERISTICS:
 - RATING: 20V, 1A Min.
 - CONTACT RESISTANCE: 50 MILLIOHMS Max. FOR INITIAL, 80 MILLIOHMS Max. AFTER 5000 CYCLES.
 - INSULATION RESISTANCE: 100 MEGAOHMS Min. BY 500V DC AFTER 1 MINUTE.
 - DIELECTRIC WITHSTANDING VOLTAGE: 500V RMS AFTER 1 MINUTE.
- MECHANICAL CHARACTERISTICS:
 - INSERTION FORCE : 0.3~3.0 KGF(2.94~29.4N)
 - WITHDRAWAL FORCE : 0.3~3.0 KGF(2.94~29.4N)
- LIFE TEST: 5,000 CYCLES MIN.

PART NO.	PLATING
PJ-3547-G	Ag
PJ-3547-A	Au

Symbol	Item	Quantity	Material/Spec	Finish
⊕	HOUSING	1	HIGH TEMP.	Black
⊙	TERMINAL 4	1	COPPER ALLOY t=0.20	SEE TABL
⊙	TERMINAL 3	1	COPPER ALLOY t=0.20	SEE TABL
⊙	TERMINAL 2	2	COPPER ALLOY t=0.20	SEE TABL
⊙	TERMINAL 1	1	COPPER ALLOY t=0.20	SEE TABL

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	PART NO.: PJ-3547-X
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	

广东星坤科技股份有限公司
PGB LAYOUT FOR VIEW
TOLERANCES: ±0.05

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISIC
	1/1	A0

文件工程章