



Temperature range: -40°C~+125°C
 温度范围: -40°C~+125°C

K 284162 T M - P SN - M
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Category:M-Male Terminal
- 5.Material:P-Phosphor Bronze
- 6.Palting:SN-Plated Tin
- 7.Special No:M-Low foot

K284162TM-PSN-M	Phosphor Bronze	AWG#24~18	K284162HF
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 5.0mm Automobile connector
DWN	VIEW:	PART NO.: K284162TM-PSN-M
CHKD	UNIT: mm/in	DWG NO.: X-K284162TM-PSN-M
APPD	SIZE: A4	WEIGHT SHEET REVISION
		1/1 A0



XKB INDUSTRIAL PRECISION CO., LIMITED

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	

Δx					
Δx					
Δx					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	
REVISIONS					