


SEC:A-A



SEC:B-B

Temperature range: -40°C~+125°C
 温度范围: -40°C~+125°C

K 284162 T F - P SN - B
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category:T-Terminal
- 4.Category:F-Female Terminal
- 5.Material:P-Phosphor Bronze
- 6.Plating:SN-Plated Tin
- 7.Special No:B-Glass B Terminal

K284162TF-PSN-B	Phosphor Bronze	AWG#24~18	K284162H
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 5.0mm Automobile connector
DWN	VIEW:	PART NO.: K284162TF-PSN-B
CHKD	UNIT: mm/in	DWG NO.: X-K284162TF-PSN-B
APPD	SIZE: A4	

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
	REVISIONS				

XKIB

XKB INDUSTRIAL PRECISION CO., LIMITED