


P.C.B LAYOUT

DC-002	DC-002-1
4	4
5	5
3	3

SCHEMATIC

MATAL	X
SUS	0.2mm
PBS	0.25mm

PIN	φ1.0	φ1.3	φ1.65
APPD.			<input checked="" type="checkbox"/>



					TOLERANCE UNLESS SPECIFIED							
NO.	PART NAME	MATERIAL	QTY	FINISHING	UP TO 5mm: ±0.1	ANGULAR ±1°	△	2013.9.3	依据ECN1309001	huli		
6	PING	BRASS	1	Ni PLATED	ABOVE 5mm: ±0.2		NO	DATE	REVISIONS	BY	APPD	
5	3#SPRING	PBS/SUS	1	Ag PLATED	TITLE:DC JACK			UNIT : MM	ROHS COMPLIANT	DWN		
4	5#CURVE PIECE	BRASS	1	Ag PLATED	MODEL:DC-002 1.65			SCALE: 5:1	CHK'D			
3	4#FLAT PIECE	BRASS △	1	Ag PLATED	<b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司			APPD				
2	COVER	PBT	1	BLACK				PRO.AGL:			REV : A	
1	CASE	PBT/PA9T	1	BLACK								