



Recommended PCB Layout (Tolerance ±0.05)
(Copper-sided View)

PIN	Ø2.0	Ø2.35	Ø2.5



DC MATE PLUG

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		1	DATE	REVISIONS	BY	APPD
					UP TO 5mm: ±0.1	ANGULAR ±1°					
6	SHUNT TERMINAL [2]	BRASS	1	Sn-PLATED	UP TO 5mm: ±0.1	ANGULAR ±1°	1				
5	TIP SPRING [1]	SUS	1	Sn-PLATED	ABOVE 5mm: ±0.2	±1°	NO				
4	CENTER PIN CONTACT [3]	BRASS	1	Sn-PLATED	TITLE: DC JACK		UNIT : MM	ROHS COMPLIANT	DWN		
3	CENTER PIN	BRASS	1	Sn-PLATED	MODEL: DC-014 2.0		SCALE: 1:1	CHK'D			
2	COVER	PCB	1		HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司			APPD			
1	HOUSING	PBT	1				PRO.AGL:		REV :A0		