



|       |      |      |
|-------|------|------|
| PIN   | φ1.0 | φ1.3 |
| APPD. |      |      |

|     |               |          |     | TOLERANCE UNLESS SPECIFIED |                                      |    |            |                |         |    |      |
|-----|---------------|----------|-----|----------------------------|--------------------------------------|----|------------|----------------|---------|----|------|
|     |               |          |     | UP TO 5mm: ±0.1            | ANGULAR                              |    |            |                |         |    |      |
|     |               |          |     | ABOVE 5mm: ±0.2            | ±1°                                  | NO | DATE       | REVISIONS      |         | BY | APPD |
| 5   | PING          | BRASS    | 1   | Ni PLATED                  | TITLE:DC JACK                        |    | UNIT : MM  | ROHS COMPLIANT | DWN     |    |      |
| 4   | 2#SPRING      | SUS      | 1   | Ag PLATED                  | MODEL: DC-045 1.3                    |    | SCALE: 6:1 | CHK'D          |         |    |      |
| 3   | 4#FLAT PIECE  | BRASS    | 1   | Ag PLATED                  | HOOYA ELECTRONIC CO. LTD<br>皓宇电子有限公司 |    | APPD       |                |         |    |      |
| 2   | 3#CURVE PIECE | BRASS    | 1   | Ag PLATED                  |                                      |    | PRO.AGL:   |                | REV : A |    |      |
| 1   | CASE          | PA9T     | 1   | BLACK                      |                                      |    |            |                |         |    |      |
| NO. | PART NAME     | MATERIAL | QTY | FINISHING                  |                                      |    |            |                |         |    |      |