






ROHS compliant



[Schematic]

NOTES:

1.Specification:

- 1>. Operation force: 1000gf Max.
- 2>. Operation Temperature: -30 °C to +85°C.
- 3>. Storage Temperature: -40 °C to +85°C.
- 4>. Mechanical Life: 3000 cycles operations.
- 5>. Resistance to Soldering: 260 ±5°C for 3-5 Seconds.

2.PLATING:


- 1>. GOLD Flash 1u" (min) SOLDERTAIL,
3u" GOLD PLATING ON THE CONTACT AREA.

3.ELECTRICAL:

- 1>. Non-switch Rating: 100mA at 50V DC.
- 2>. Switching Rating: 25mA at 24V DC.
- 3>. Contact Resistance: Initial 50mΩ Max.
Contact Resistance: After life 100mΩ Max.
- 4>. Insulation Resistance: 1000MΩ Min at 50VDC.
- 5>. Dielectric Strength: 500V AC for 60seconds.
- 6>. Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DSIC XX L S G E T



5.PACKING: 29pcs/Tube, 2320pcs/Box.

| REV. | ECN NO. | DRAWN | DATE |
|------|---------|-------|------|
| | | | |
| | | | |

| | | | | | | | |
|----------|--------|-------|------------|----------|-----------|----------------|--------------------------|
| Drawing | dengkg | Date | 2018.03.24 | LINER | ANGLES | PRODUCT Family | DSIC Series Pitch 2.54mm |
| Check | zhong | Scale | 4:1 | >0±0.05 | >0° ±0.5° | PRAT NO. | DSIC07LSGET |
| Approved | | Unit | MM | >1±0.10 | >5° ±1.0° | FILE NO. | KE-DSIC-007-S-A |
| Size | A4 | Rev. | A | >10±0.30 | | PROJECTION | |

东莞市康深电子科技有限公司
 Kongshen Electronics technology co., LTD.