



PCB Layout



Technical Data
 Material:
 Contact material: Brass
 Plating: Gold Flash
 Insulator material: Black polyester UL94V-0
 Standard: PA6T+30%G. F

Electrical:

Current rating: 3Amps/contact max.
 Contact resistance: $\leq 20m\ \Omega$ /contact
 Insulation resistance: $\geq 1000M\ \Omega$ at V=100V
 Withstanding voltage: 550V AC/minute

Mechanical:

Soldering temperature: $+260^{\circ}C$, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20

PIN NUMBER	A (mm)	B (mm)	C (mm)
6P	15.24	5.08	12.94
8P	17.78	7.62	15.48
10P	20.32	10.16	18.02
12P	22.86	12.70	20.56
14P	25.40	15.24	23.10
16P	27.94	17.78	25.64
18P	30.48	20.32	28.18
20P	33.02	22.86	30.72
22P	35.56	25.40	33.26
24P	38.10	27.94	35.80
26P	40.64	30.48	38.34
28P	43.18	33.02	40.88
30P	45.72	35.56	43.42
32P	48.26	38.10	45.96
34P	50.80	40.64	48.50
36P	53.34	43.18	51.04
40P	58.42	48.26	56.12
44P	63.50	53.34	61.20
50P	71.12	60.96	68.82
60P	83.82	73.66	81.52
64P	88.90	78.74	86.60

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/5/4	DN254P-2X□-L0	
CHECKED			TITLE: 筒生2.54 nP SM	
APPROVALS			PART NO.	
DRAWN		DATE	UNIT: mm	SCALE: 1:1
CHECKED			DRAWING NO.	SHEET 1 OF 1
APPROVALS				PROJ.
TOLERANCES ARE				
30 ^{±0.15}	±0.30	ANGLE		
10 ^{±0.10}	±0.20			
5 ^{±0.10}	±0.15	±2°		
ECN NO.	REV.	DATE.	DESCRIPTION.	
	A		NEW	

DEALON 德之隆®
 ELECTRONICS CO.,LTD