



Mechanical:
Soldering temperature: +220°C, 4s max
UNSPECIFIED TOLERANCE: ±0.20

Technical Data
Material: Brass
Contact material: Brass
Plating: Gold Flash
Insulator material: Black polyester UL94V-0
Standard: PBT+30%G.F

Electrical:
Current rating: 3Amps/contact max.
Contact resistance: ≤20mΩ/contact
Insulation resistance: ≥1000MΩ at V=100V
Withstanding voltage: 550V AC/minute

PTN NUMBER	A (mm)	B (mm)	C (mm)
6P	15.24	5.08	12.94
8P	17.78	7.62	15.48
10P	20.32	10.16	18.02
12P	22.86	12.70	20.56
14P	25.40	15.24	23.10
16P	27.94	17.78	25.64
18P	30.48	20.32	28.18
20P	33.02	22.86	30.72
22P	35.56	25.40	33.26
24P	38.10	27.94	35.80
26P	40.64	30.48	38.34
28P	43.18	33.02	40.88
30P	45.72	35.56	43.42
32P	48.26	38.10	45.96
34P	50.80	40.64	48.50
36P	53.34	43.18	51.04
40P	58.42	48.26	56.12
44P	63.50	53.34	61.20
50P	71.12	60.96	68.82
60P	83.82	73.66	81.52
64P	88.90	78.74	86.60

APPROVALS		DATE	DRAWING NO.	
DRAWN	G.M.Chen	2015/5/4	DS254P-2X□-L0	
CHECKED			TITLE:	
APPROVALS			筒生2.54 nP 90度	
TOLERANCES ARE		ANGLE	SCALE: 1:1	SHEET 1 OF 1
10 ^{+0.10}	±0.20	±2°		PROJ.
5 ^{+0.10}	±0.10			
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	

DEALON 德之隆®
ELECTRONICS CO.,LTD