


PCB Layout



Technical Data
 Material:
 Contact material:Brass
 Plating:Gold Flash
 Insulator material:Black polyester UL94V-0
 Standard:PBT+30%G.F

Electrical:
 Current rating:3amps/contact max.
 Contact resistance: $\leq 20m\Omega$ /contact
 Insulation resistance: $\geq 1000M\Omega$ at V=100V
 Withstanding Voltage:550V AC/minute

Mechanical:
 Soldering temperature: +220°C, 4s max
 UNSPECIFIED TOLERANCE: ± 0.20

PIN NUMBER	A (mm)	B (mm)	C (mm)
6P	15.24	5.08	12.94
8P	17.78	7.62	15.48
10P	20.32	10.16	18.02
12P	22.86	12.70	20.56
14P	25.40	15.24	23.10
16P	27.94	17.78	25.64
18P	30.48	20.32	28.18
20P	33.02	22.86	30.72
22P	35.56	25.40	33.26
24P	38.10	27.94	35.80
26P	40.64	30.48	38.34
28P	43.18	33.02	40.88
30P	45.72	35.56	43.42
32P	48.26	38.10	45.96
34P	50.80	40.64	48.50
36P	53.34	43.18	51.04
40P	58.42	48.26	56.12
44P	63.50	53.34	61.20
50P	71.12	60.96	68.82
60P	83.82	73.66	81.52
64P	88.90	78.74	86.60

APPROVALS		DATE	TITLE:	
DRAWN	G.M.Chen	2015/5/4	筒生2.54 nP 90度	
CHECKED			DW2054P-2X□-10	
APPROVALS				
PART NO. _____				
UNIT: mm				
SCALE: 1:1				
DRAWING NO. _____				
SHEET 1 OF 1				
PROJ. _____				
TOLERANCES ARE				
30 ^{±0.15} ±0.30 ANGLE				
10 ^{±0.10} ±0.20				
5 ^{±0.10} ±0.15				
±2				
DRAWING NO. _____				
SHEET 1 OF 1				
PROJ. _____				
DESCRIPTION. NEW				
CHANGE. _____				
CHECK. _____				
APPRO. _____				
ECN NO. _____				
REV. _____				
DATE. _____				

DEALON 德之隆
 ELECTRONICS CO.,LTD