



Current rating: 3A AC/DC
 额定电流: 3A AC/DC
 Temperature range: -40°C~+125°C
 温度范围: -40°C~+125°C

K 137635 T F - P SN - A
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.K: XKBTEK-Car Connector
- 2.XKB Series No
- 3.Category: T-Terminal
- 4.Category: F-Female Terminal
- 5.Material: P-Phosphor Bronze
- 6.Plating: SN-Plating Tin
- 7.Special No: A-Class A terminal



SEC:A-A



SEC:B-B

K137635TF-PSN-A	Phosphor Bronze	AWG#28~24	K137635HM
PART NO	Material	Wire Range	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 2.2mm Automobile connector
DWN	VIEW:	PART NO.: K137635TF-PSN-A
CHKD	UNIT: mm/in	DWG NO.: X-K137635TF-PSN-A
APPD	SIZE: A4	

					ANGULAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0