




REV.	ECON NO.	DESCRIPTION	DATE	DESIGN
A				

NOTES:
 CURRENT RATING: 2A AC/DC.
 VOLTAGE RATING: 125V AC/DC
 TEMPERATURE RANGE: -40°C~+105°C.
 CONTACT RESISTANCE: 20MΩ Max.
 INSULATION RESISTANCE: 1000MΩ Min.
 WITHSTANDING VOLTAGE: 800V AC/MINUTE.
 MATERIAL: PA66+GF15%. UL94V-0.



Recommended P.C.B Layout(Top Side)



PART NO.	DIMENSION	
	A	B
A2004WR-02P	2.00	6.00
A2004WR-03P	4.00	8.00
A2004WR-04P	6.00	10.00
A2004WR-05P	8.00	12.00
A2004WR-06P	10.00	14.00
A2004WR-07P	12.00	16.00
A2004WR-08P	14.00	18.00
A2004WR-09P	16.00	20.00
A2004WR-10P	18.00	22.00
A2004WR-11P	20.00	24.00
A2004WR-12P	22.00	26.00
A2004WR-13P	24.00	28.00
A2004WR-14P	26.00	30.00
A2004WR-15P	28.00	32.00

DIM	TOL	DIM	TOL
X	/	X.	/
XX	0.25	XX	
XXX	0.15	XXX	
XXXX	0.10	XXXX	

CNJM Joint More Precision electronics Co.,Ltd.

DRAW. NO.	DATE	P/N NO.	DRAW. NAME:
DESIGN: 陈雪峰	2017.06.03	A2004WR-NP	2.0mm pitch wifer
CHECK: 杨 烨			
REVIEW:		REV. A/1	SCALE 1:1
			UNIT: mm
			SHEET: 1 OF 1