





REV.	ECN NO.	DESCRIPTION	DATE	DESIGN
A		变更料号	16/11/22	苏亮



Specifications:  
 Current rating: 3A AC/DC.  
 Voltage rating: 250V AC/DC  
 Temperature range:  $-40^{\circ}\text{C} \sim +105^{\circ}\text{C}$ .  
 Contact resistance: 10MΩ Max.  
 Insulation resistance: 1000MΩ Min.  
 Withstanding voltage: 800V AC/minute.  
 Material: pa9t 94v0.

PART NO.	Dimensions	
	A	B
A2006wV-S-2X02P	6.00	2.00
A2006wV-S-2X03P	8.00	4.00
A2006wV-S-2X04P	10.00	6.00
A2006wV-S-2X05P	12.00	8.00
A2006wV-S-2X06P	14.00	10.00
A2006wV-S-2X07P	16.00	12.00
A2006wV-S-2X08P	18.00	14.00
A2006wV-S-2X09P	20.00	16.00
A2006wV-S-2X10P	22.00	18.00
A2006wV-S-2X11P	24.00	20.00
A2006wV-S-2X12P	26.00	22.00
A2006wV-S-2X13P	28.00	24.00
A2006wV-S-2X14P	30.00	26.00
A2006wV-S-2X15P	32.00	28.00
A2006wV-S-2X16P	34.00	30.00
A2006wV-S-2X17P	36.00	32.00
A2006wV-S-2X18P	38.00	34.00
A2006wV-S-2X19P	40.00	36.00
A2006wV-S-2X20P	42.00	38.00



2P 视图

**CNJM** Joint More Precision electronics Co.,Ltd.

DIM	TOL	DIM	TOL
X.	/	X*	/
X.X	0.25	X.X*	
X.XX	0.15	X.XX*	
X.XXX	0.10	X.XXX*	/

DRAW NO.	DATE	P/N NO:	DRAW NAME:
DESIGN: 陈雪峰	2017.06.03	A2006wV-S-2XNP	2.0mm PITCH 180° DUAL ROW WAFER -SMT YTYPE
CHECK: 杨焯		REV. A/1	SCALE 1:1
REVIEW:		UNIT: mm	SHEET: 1 OF 1