


SPECIFICATIONS

Current Rating: 1A AC,DC
 Voltage Rating: 125V AC,DC
 Temperature Range: -25°C~+85°C
 Resistance: 20mΩ Max.
 Insulation Resistance: 100MΩ Min.
 Withstanding Voltage: 500V AC/minute
 Pin Material: Phosphor Bronze/ Gold-plated
 Solder Tabs: Brass/Gold-plated
 Material: Nylon 6T, UL94V-0
 Color: Natural(Beige)



PART NO.	Dimensions		
	A	B	C
L125RS-02PW	1.25	7.65	8.07
L125RS-03PW	2.50	8.90	9.32
L125RS-04PW	3.75	10.15	10.57
L125RS-05PW	5.00	11.40	11.82
L125RS-06PW	6.25	12.65	13.07
L125RS-07PW	7.50	13.90	14.32
L125RS-08PW	8.75	15.15	15.57
L125RS-09PW	10.00	16.40	16.82
L125RS-10PW	11.25	17.65	18.07
L125RS-11PW	12.50	18.90	19.32
L125RS-12PW	13.75	20.15	20.57
L125RS-13PW	16.25	22.65	23.07
L125RS-15PW	17.50	23.90	24.32
L125RS-16PW	18.75	25.15	25.57
L125RS-20PW	23.75	30.15	30.57
L125RS-30PW	36.25	42.65	43.07

APPROVALS		DATE	TITLE:	
DRAWN	G.M.Chen	2015/7/17	DC POWER JACKS	
CHECKED			L125RS-XXPW	
APPROVALS			PART NO.	
TOLERANCES ARE		30 ^{+0.15} ±	±0.30	ANGLE
		10 ^{+0.10} ±	±0.20	UNIT: mm
		5 ^{+0.10} ±	±0.15	SCALE: 1:1
ECN NO.	REV.	DATE.	DESCRIPTION.	SHEET 1 OF 1
	A		NEW	PROJ

