









Customer NO:		DOSIN-801-0009		
REV	DESCRIPTION	DWN	DATE	APPROVEN
A	First issue	Mr.chen	2016/3/03	John kine
B				



Specifications:

- IMPEDANCE: 50 Ohms
- Frequency range: 0~3GHZ
- VSWR: 1.5MAX
- Working voltage: 500V rms @ sea level
- Insulation resistance: 5000 Ohms min
- Temperature range: -55°C TO +155°C
- Relative temperature: ≤95% (40° C ± 2° C)

1	BODY	Zinc	NICKEL	4	NOTE:	Tolerance	X.	±0.15	Dosin Industrial (HK) Co. Ltd 东莞市德索五金电子制品有限公司 Dosin Hardware Electronics Co., Ltd	E-mail: dosin2005@163.com	
2	SOLDEI COLUMN	Iron	NICKEL	4			X.X	±0.10		dosin2005@dosin-china.com	
3	IRON PLATES	Iron	NICKEL	1			X.XX	±0.05		Web: http://www.dosinconn.com	
4	PIN	Brass	NICKEL	4			Angular	±5°		TEL: (0086) 769-81153906 FAX: (0086) 769-81875836	
5	INSULATOI	POM	White	4	DRAWN Zelin.chen	View		Name: BNC Jack 1*4 Port 90° PCB Mount	DateTime	CAD FILE	SHEET: 1 OF 1
6	PANEL	PBT/ABS	Black	1							
10	Component Number	Material	Finish	QTY	APPROVALS John	SCALE	1:1	DateTime 2016/3/03	H/company drawings/BD		