








| Product NO. | | DOSIN-801-0018 | | |
|-------------|---|----------------|------------|-----------|
| REV | DESCRIPTION | DWN | DATE | APPROVEN |
| A | First issue | JIM | 2012/11/02 | John kine |
| B | 80μ"100μ" Tin plating over 80μ"100μ" Ni under plate | chen | 2022/01/12 | John kine |



Specifications

Impedance: 50 Ohms
 Frequency Range: DC~3G
 VSWR: 1.3MAX
 Working Voltage: 500V rms @ sea level
 Insulation Resistance: 5000 Ohms min
 Temperature Range: -55°C T0 +155°C
 Relative Temperature: ≤95%(40° C±2° C)
 Drawings products are in line with ROHS standards

| | | | | |
|----|---------------|----------|---|-----|
| 5 | Solder column | Iron | 80μ"100μ" Tin plating over 80μ"100μ" Ni under plate | 8 |
| 4 | IRON PLATES | Iron | NICKEL Ni:80-100μ" | 1 |
| 3 | PANEL | PBT | BLACK | 1 |
| 2 | PIN | BRASS | NICKEL Ni:80-100μ" | 8 |
| 1 | BODY | ZINC | NICKEL CU:300-500μ"Ni:80-100μ" | 8 |
| NO | DESCRIPTION | MATERIAL | FINISH | QTY |

NOTE:

| | | | | | |
|-----------|-----------|------------|-----------|----------------------------------|--------------------------------|
| DRAWN | chen | 2022/01/12 | Tolerance | 0-6 6-30 30-120 Angular | ±0.10 ±0.20 ±0.40 ±2° |
| CHECKED | | | View | | |
| APPROVALS | John King | | UNIT | MM | |
| | | | SCALE | 1:1 | |

Dosin Industrial(H.K)Co.Ltd
 东莞市德奈五金电子有限公司
Dosin Hardware Electronics Co., Ltd

Name: BNC CONNECTOR

Product NO. DOSIN-801-0018-B

CAD FILE D/company drawings/BD

E-mail:dosin2005@163.com
 dosin2005@dosin-china.com
 Web: http://www.dosin.com
 TEL:(0086)769-81153906
 FAX:(0086)769-81875586

SHEET: 1 OF 1