



电路图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻:  $\leq 50m\Omega$
3. 操作力:  $250 \pm 30gf$
4. 行程:  $0.30 \pm 0.1mm$
5. 绝缘电阻:  $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H

操作力 E:  $250 \pm 30$

TRAVEL: IP67

Waterproof grade:  $0.3 \pm 0.1mm$

PCB. 焊接图

H	L
3.3	2.80
4.3	3.15
4.5	3.15
√5.0	3.15
7.0	3.15

				TOLERANCE UNLESS SPECIFIED									
NO.	PART NAME	MATERIAL	QTY	FINISHING	UP TO 5mm: $\pm 0.1$	ANGULAR $\pm 1^\circ$	A0	NO	DATE	REVISIONS	BY	APPD	
6	TERMINAL	BRASS	2	Ag-Plated	UP TO 5mm: $\pm 0.1$	ANGULAR $\pm 1^\circ$	A0						
5	CASE	PPA	1	BLACK	ABOVE 5mm: $\pm 0.2$								
4	REED	SUS	1	Ag-Plated									
3	WATERPROOF PAD	RUBBER	1	BLACK									
2	COVER	SUS	1										
1	BUTTON	PPA	1	BLACK/RWD									
					TITLE: TACT SWITCH MODEL: TC-00104AFB-050E				UNIT : MM	ROHS COMPLIANT	DWN	CHK'D	
					HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司				SCALE: 1:1		APPD		
									PRO.AGL:		REV :A0		