


电路图



H	
4.3	4.5
5.0	5.5
6.0	6.5
✓ 9.5	.....
13.0	13.5
14.0	15.0

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻:  $\leq 50m\Omega$
3. E(操作力):  $250 \pm 40gf$
4. 行程:  $0.45 \pm 0.1mm$
5. 绝缘电阻:  $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H



皓宇电子  
HOOYU ELECTRONICS



PCB. 焊接图

操作力 : E=250 ± 50gf

					TOLERANCE UNLESS SPECIFIED						
					UP TO 5mm: ±0.1	ANGULAR					
					ABOVE 5mm: ±0.2	±1°	1	REVISIONS		BY	APPD
6	TERMINAL	BRASS	4	Ag-Plated			NO	DATE			
5	CASE	PPA	1	BLACK	TITLE: TACT SWITCH		UNIT : MM	ROHS COMPLIANT	DWN		
4	REED	SUS	1	Ag-Plated	MODEL: TC-00121FS-095E		SCALE: 1:1	CHK'D			
3	WATERPROOF PAD	RUBBER	1	BLACK	HAOYU(HONGKONG)LIMITED		APPD				
2	COVER	PPA	1	BLACK	皓宇(香港)有限公司		PRO.AGL:				REV :A0
1	BUTTON	PPA	1	BLACK							
NO.	PART NAME	MATERIAL	QTY	FINISHING							