


电路图


主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: ≤50mΩ
3. E(操作力: 250±50gf)
4. 行程: 0.3±0.1mm
5. 绝缘电阻: ≥100MΩ
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H



PCB. 焊接图

操作力: E=250 ± 50gf



H	
4.3	4.5
5.0	5.5
6.0	6.5
7.0	7.5
8.0	8.5
9.0	9.5

NO.	PART NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO		DATE	REVISIONS		BY	APPD
8					UP TO 5mm: ±0.1	ANGULAR	1						
7					ABOVE 5mm: ±0.2	±1°	NO						
6	CONTACT	BRASS	4	Ag-PLATED	TITLE: TACT SWITCH				UNIT : MM	ROHS COMPLIANT	DWN		
5	CASE	PPA	1	BLACK	MODEL: TC-06104F-070E				SCALE: 1:1		CHK'D		
4	REED	SUS	1	Ag-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
3	WATERPROOF PAD	RUBBER	1	BLACK									
2	COVER PLATE	PPA	1	BLACK									
1	BUTTON	PPA	1	BLACK									
									PRO.AGL:			REV :A0	