


电路图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻:  $\leq 50m\Omega$
3. F(操作力):  $350 \pm 30gf$
4. 行程:  $0.30 \pm 0.1mm$
5. 绝缘电阻:  $\geq 100M\Omega$
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H

操作力:  $F=350 \pm 50gf$

H	
4.3	4.5 ✓
5.0	



PCB. 焊接图

				TOLERANCE UNLESS SPECIFIED							
				UP TO 5mm: $\pm 0.1$	ANGULAR	1					
				ABOVE 5mm: $\pm 0.2$	$\pm 1^\circ$	NO	DATE	REVISIONS		BY	APPD
6	TERMINAL	BRASS	2	Ag-Plated	TITLE: TACT SWITCH		UNIT: MM	ROHS COMPLIANT	DWN		
5	CASE	PPA	1	BLACK	MODEL: TC-06104FSB-045F		SCALE: 1:1	CHK'D			
4	REED	SUS	1	Ag-Plated	<b>HAOYU(HONGKONG)LIMITED</b> 皓宇(香港)有限公司		APPD				
3	WATERPROOF PAD	RUBBER	1	BLACK			PRO.AGL:		REV :A0		
2	COVER	SUS	1								
1	BUTTON	PPA	1	BLACK/RWD							
NO.	PART NAME	MATERIAL	QTY	FINISHING							