



电路图

主要技术规格:

1. 额定值: 50mA DC12V
2. 接触电阻: ≤50mΩ
3. E(操作力): 250±30gf
4. 行程: 0.30±0.1mm
5. 绝缘电阻: ≥100MΩ
6. 抗电强度: 250V 50HZ 1Min.
7. 寿命: 100,000 Cycles
8. 防水等级: IP67
9. 防银迁移: 60V, 85°C, 90%RH/60H

操作力: E=250 ± 50gf



PCB. 焊接图

H	
4.3	4.5
5.0	

NO.	PART	NAME	MATERIAL	QTY	FINISHING	TOLERANCE UNLESS SPECIFIED		NO	DATE	REVISIONS		BY	APPD	
6	TERMINAL		BRASS	2	Ag-Plated	UP TO 5mm: ±0.1	ANGULAR	1						
5	CASE		PPA	1	BLACK	ABOVE 5mm: ±0.2	±1°							
4	REED		SUS	1	Ag-Plated	TITLE: TACT SWITCH				UNIT: MM	ROHS	DWN		
3	WATERPROOF PAD		RUBBER	1	BLACK	MODEL: TC-06104FSB-050E				SCALE: 1:1	COMPLIANT	CHK'D		
2	COVER		SUS	1		HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司						APPD		
1	BUTTON		PPA	1	BLACK/RWD									
												PRO.AGL:		REV :A0