

Specifications:








规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating:1A AC/DC
 额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
 耐受电压: 500V AC/分钟
Temperature range:-40℃~+105℃
 温度范围: -40℃~+105℃
Insulation resistance:≥100MΩ
 绝缘电阻: ≥100MΩ
Contact resistance:≤20mΩ
 接触电阻: ≤20mΩ

X1270 H -2xXX -PT V01
 ① ② ③ ④ ⑤

1. Series No
2. Category:H-HSG
3. Row No-Pin No:2xXX-2x03P~2x40P
4. Material:PT:PBT UL94V-0
5. Plating Category: V01-All Gold Flash

NUMBER OF POSITIONS	DIMENSION	
	A	B
06	2.54	8.00
08	3.81	9.27
10	5.08	10.54
12	6.35	11.81
14	7.62	13.08
16	8.89	14.35
20	11.43	16.89
24	13.97	19.43
26	15.24	20.70
30	17.78	23.24
32	19.05	24.51
34	20.32	25.78

36	21.59	27.05
40	24.13	29.59
44	26.67	32.13
50	30.48	35.94
60	36.83	42.29
64	39.37	44.83
66	40.64	46.10
68	41.91	47.37
70	43.18	48.64
74	45.72	51.18
76	46.99	52.45
80	49.53	54.99



X1270H-2xXX-PTV01	PBT UL 94V-0	Phosphor Bronze	Gold Flash	X1270W
PART NO	Material	Material(Pin And Solder Tabs)	Finish(Pin And Solder Tabs)	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 1.27mm BTB Style Connectors
DWN	VIEW:	PART NO.:
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X1270H-2xXX-PTV01
XKB INDUSTRIAL PRECISION CO., LIMITED		WEIGHT
		SHEET
		REVISION
		1/1
		A0

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
				ANGULAR ±5°
				L ≤ 4 ±0.2
				4 < L ≤ 16 ±0.3
				16 < L ≤ 63 ±0.4
				L > 63 ±0.5

