




P.C.B LAYOUT
TOP VIEW



SCHEMATIC

H
4.3
5.3

操作力 E:250±50

					TOLERANCE UNLESS SPECIFIED									
					UP TO 5mm: ±0.1	ANGULAR	1							
					ABOVE 5mm: ±0.2	±1°	NO	DATE	REVISIONS		BY	APPD		
5	SPRING	SUS	1	Ag-Plating	TITLE: TACT SWITCH			UNIT : MM	ROHS	DWN				
4	CONTACT FOOT	BRASS	2	Ag-Plating	MODEL: TC-00302-043E			SCALE: 1:1	COMPLIANT	CHK'D				
3	COAT	BRASS	1	Ni-Plating	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
2	BUTTON	PA66	1	BLACK								PRO.AGL:		REV :A0
1	HOUSING	PA66	1	BLACK										
NO.	PART NAME	MATERIAL	QTY	FINISHING										