



RoHS&REACH

ECN NO.	DESCRIPTION	DATE
A-1	更新外形及尺寸	2020.11.16
A-2	更新细节	2021.11.28





材料Material:

- 外壳材质: PBT, PA66, PA46 (UL 94V-0)
Housing Material: PBT, PA66, PA46 (UL 94V-0)
- 触点材料: 圆针直径0.46mm磷青铜; 镀镍后镀金
Contact Material: Round Pins-0.46mm Diameter Phosphor Bronze; Gold Plating Over Nickel

电气Electrical

- 额定电压: 交流125伏
Voltage Rating: 125 VAC Rms
- 额定电流: 1.5安培
Current Rating: 1.5 AMP
- 接触电阻: 最大30毫欧
Contact Resistance: 30 Milliohms Max
- 绝缘电阻: 直流500V下, 绝缘最小500兆欧
Insulation Resistance: 500 megohms min @500V DC
- 绝缘耐压: 交流60Hz 1000V下, 1分钟
Dielectric Withstanding Resistance: 1000V AC Rms 60Hz. 1Min
- 耐久: 插拔750次以上
Durability: 750 Cycles Min
- 工作温度: -40℃~+85℃
Operation Temperature: -40℃~+85℃



PCB LAYOUT

5503 - X X X X X X X

Positions	Contacts	Ports	Panel	Plastic	Color	Gold Plating
6	2, 4 or 6	2-1x2 3-1x3 4-1x4 5-1x5 N-1xN	0-w/O panel 1-w/ Panel	1-PBT 2-PA66 3-PA46	1-Black 2-Gary 3-Other	1-G/Fu" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"

未注公差		设计	X.C.S	比例	1:1
尺寸标注	公差				
	长度	审核		单位	mm
	角度				
.X	±0.25	批准		图幅	A4
.X	±0.20				
.XX	±0.15	角法		版本	A-2
.XXX	±0.10				

恒连电子科技有限公司
EVERCOM ELECTRONIC TECHNOLOGY CO., LTD
<http://www.chinarj45.com>

产品型号 5503 1x4 6P60 有边
产品编号 5503-6641XXX
图纸编号 HL215506642

第1页 共1页