




RoHS&REACH

REV.	ECN NO.	DESCRIPTION	REVISED	DATE
				2021.7.21



MATERIAL:


1. HOUSING MATERIAL: PBT
2. CONTACT MATERIAL: ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE;GOLD PLATING OVER NICKEL, 30U
3. WIRE:UL 1061 26#

ELECTRICAL

1. VOLTAGE RATING : 125 VAC RMS
2. CURRENT RATING: 1.5 AMP
3. CONTACT RESISTANCE: 40 MILLIOHMS MAX
4. INSULATION RESISTANCE: 500 MEGOHMS MIN @500V DC
5. DIELECTRIC WITHSTANDING RESISTANCE: 1000V AC RMS 60Hz. 1MIN
6. DURABILITY: 750 CYCLES MIN
7. TEMPERATURE: -40° C/+85° C
8. CRIMPING STRENGTH:2.3KG MIN

616E- X X - X X X L: Wire Length

Positions	Contacts	Wire Style	Color	GP
4	2 or 4	1 - 24AWG 2 - 26AWG 3 - 28AWG	1-Black 2-Gray 3-Other	1-G/Fu" 2-3u" 3-6u" 4-15u" 5-30u" 6-50u"



4	反端	4	黄铜	
3	金线	4	磷铜 30u"	
2	电子线	4	UL 1061 26AWG	扭线沾锡
1	616E塑壳	1	PBT	灰色
序号	物料名称	数量	材质	备注

线序	颜色	长度	剥头
4	黑	110mm	3.0mm
3	红	200mm	3.0mm
2	绿	200mm	3.0mm
1	黄	110mm	3.0mm

除非另行说明, 否则公差按照下表		设计	RD	比例	1: 1
尺寸标注	公差	审核	批准	单位	mm
	长度			±0.25	±2.0°
.X	±0.25			版本	A-0
.XX	±0.20			图数	第1页 共1页
.XXX	±0.15			产品型号	616E灰 4P4C 黄黑110 红绿200
	±0.10			产品编号	

恒连电子科技有限公司
 EVERCOM ELECTRONIC TECHNOLOGY CO., LTD
<http://www.chinarj45.com>

图号: 616E灰 4P4C 黄黑110 红绿200