





RoHS&REACH




NOTES:

MATERIAL:

- 1. HOUSING MATERIAL : ABS(UL 94V-0)
- 2. CONTACT MATERIAL : ROUND PINS-0.46mm DIAMETER PHOSPHOR BRONZE; GOLD PLATING OVER NICKEL
- 3. WIRES : UL 1061 26#

ELECTRICAL/PHYSICAL:

- 1. VOLTAGE RATING : 125 VAC RMS
- 2. CURRENT RATING : 1.5 AMP
- 3. CONTACT RESISTANCE : 30 MILLIOHMS MAX2
- 4. INSULATION RESISTANCE : 500 MEGOHMS MIN @500V DC
- 5. DIELECTRIC WITHSTANDING RISTANCE : 1000V AC RMS 60Hz. 1MIN
- 6. DURABILITY : 750 CYCLES MIN
- 7. TEMPERATURE : -40°C/+85°C



除非另行说明, 否则公差按照下表			设计	RD	比例	1:1
尺寸标注	公差		审核	批准	单位	mm
	长度	角度			图幅	A4
.X	±0.25	±2.0°	第三视角投影	图数	版本	A-0
.X	±0.20	±1.5°			图数	第1页 共1页
.XX	±0.15	±1.0°			产品型号	HL 616MS 4P4C
.XXX	±0.10	±0.5°			产品编号	


恒连电子科技有限公司
 HENGLIAN ELECTRONIC TECHNOLOGY CO.,LTD
<http://www.chinarj45.com>