






技术要求:

1. 额定电负荷 : DC 30V 0.5A;
2. 接触电阻 : $\leq 0.06\Omega$;
3. 绝缘电阻 : $\geq 100M\Omega$ (DC250V);
4. 耐压 : 500VAC
5. 插力 : 3-30N
6. 拔力 : 3-30N
7. 寿命 : 5,000



线路板开孔尺寸
P.C.B LAYOUT



SCHEMATIC

PJ-392B	PJ-392B-1	PJ-392B-2	PJ-392B-3	PJ-392B-4	PJ-392B-5	PJ-392B-6	PJ-392B-7	PJ-392B-8	PJ-392B-9	PJ-392B-10	PJ-392B-11

9	PJ392B 底座	PA46	1	BLACK										
8	PJ392B 4#弹片	SUS301	1	AU-PLATED										
7	PJ392B 2#接触片	BRASS	1	AU-PLATED										
6	PJ392B 2#接触片	BRASS	1	AU-PLATED	TOLERANCE UNLESS SPECIFIED									
5	PJ392B 3#接触片	BRASS	1	AU-PLATED	UP TO 5mm: ± 0.1	ANGULAR	A0	2019.11.29	首次发行		GYW			
4	PJ392B 1#接触片	BRASS	1	AU-PLATED	ABOVE 5mm: ± 0.2	$\pm 1^\circ$	NO	DATE	REVISIONS		BY APPD			
3	PJ392B 5#弹片	SUS301	1	AU-PLATED	TITLE: PHONE JACK			UNIT : MM	ROHS	DWN				
2	PJ392B 5#弹片	SUS301	1	AU-PLATED	MODEL: PJ-392B-2			SCALE: 3:1	COMPLIANT	CHK'D				
1	PJ392B 5#弹片	SUS301	1	AU-PLATED	HAOYU(HONGKONG)LIMITED 皓宇(香港)有限公司							APPD		
NO.	PART NAME	MATERIAL	QTY	FINISHING								PRO.AGL:		REV :A0