






ROHS compliant

REV.	ECN NO.	DRAWN	DATE



NOTES:

1.MECHANICAL:

- 1>.Operation force: 1000gf Max.
- 2>.Operation Temperature: -30 °C to +85 °C.
- 3>.Storage Temperature: -40 °C to +85 °C.
- 4>.Mechanical Life: 3000 cycles operations.
- 5>.Resistance to Soldering: 260 ±5 °C for 3-5 Seconds.
- 6>.Please keep switch in "OFF" when welding.

2.MATERIAL:

- 1>.Base: UL94V-0 PBT Thermoplastic / Color:Black.
- 2>.COVER: UL94V-0 PBT Thermoplastic / Color:Red, Black, Blue.
- 3>.ACTUATOR: UL94V-0 PBT High Thermoplastic / Color: White.
- 4>.TERMINAL: Copper alloy with gold plating for1.5u".

3.ELECTRICAL:

- 1>.Non-switching Rating:100mA at 50VDC.
- 2>.Switching Rating: 25mA at 24VDC.
- 3>.Contact Resistance: Inital 50mΩ Max.
Contact Resistance: After life 100mΩ Max.
- 4>.Insulation Resistance:100MΩ Min at 500VDC.
- 5>.Dielectric Strength: 500VAC for 60seconds.
- 6>.Switch Capacitance: 5PF Max at 1MHZ.

4.PART NUMBER DESCRIPTION:

DP-XX-B-T

- (包装方式: T=Tube)
- (外壳颜色: R=红色/B=蓝色/K=黑色)
- (开关位数: 01位——12位)
- (侧拨拨码开关)

5.PACKING: 22pcs/Tube, 704pcs/Box.

东莞市康深电子科技有限公司
Kongshen Electronics technology co., LTD.

Drawing	DKG	Date	2018.01.20	LINER	ANGLES	PRODUCT Family DP Series Pitch 2.54mm	
Check	TOM	Scale	3:1	>0±0.05	>0° ±0.5°	PRAT NO.	DP-08-B-T
Approved		Unit	MM	>1±0.10	>5° ±1.0°	FILE NO.	SK-DP-008-A
Size	A4	Rev.	A	>10±0.30		PROJECTION	