







N=PIN数



P.C.B LAYOUT

Material材料

Insulator塑胶: PBT (UL 94V-0)

Contact 端子: Brass黄铜

Contact plating表面镀层: Au or Sn over 50u" Ni  
里镍外金or锡

Electrical Characteristics电气特性

Current rating额定电流: 2.5Amps

Dielectric Withstanding Voltage耐压:

AC 1000V for 1 Minute.

Insulator Resistance绝缘电阻: 1000MΩ Min.

Contact Resistance接触电阻: 20MΩ Max.

Operating Temperature工作温度: -40℃~+105℃

Max. Processing Temp瞬时温度:

120℃ for 30-60 seconds

(120℃ for 10 seconds)

未注尺寸公差			PM 2.54 1*N		上海洲日电子有限公司 Shanghai Zhouri Electronics CO.,LTD 上海康司玛电子设备进出口有限公司 Shanghai KangSiMa Eletronic Equipment import and export Co.,LTD			
尺寸	公差							
X.	±0.3	±5°		版本编号	20171018 A/O			
X.X	±0.2	±3°		图纸编号	ZR20171018-291			
X.XX	±0.15			物料编号	TEL:86-21-34975176/51571121			
制图	周元金	201171018		第三视角	: 1 1			
审核	张海娜	201171018						
核准	章妹	201171018						