



■ Specifications :

- Voltage rating: 350V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -55°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing:≤40mΩ

X1515 H- XX-N0

① ② ③ ④

- ① SeriesNumber
- ② Category : H-HSG
- ③ Row No.Pin No:02-15P
- ④ Material:N0-PA66 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	4.10	3.70	09	12.00	14.60	14.20
03	3.00	5.60	5.20	10	14.0	16.10	15.70
04	4.50	7.10	6.70	11	15.0	17.60	17.20
05	6.00	8.60	8.20	12	17.0	19.10	18.70
06	7.50	10.10	9.70	13	19.0	20.60	20.20
07	9.00	11.60	11.20	14	24.0	22.10	21.70
08	10.50	13.10	12.70	15	24.0	23.60	23.20

X1511H-XX-N0	PA66 UL 94V-0	X1511T	X1511W
PARY N0	Matnal	Suitable X1B Terminal	Suitable X1B Terminal

DSND	DATE	SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connectors
DWN	DATE	VIEW:	PART NO.: X1511H-XX-N0
CHKD	DATE	UNIT: mm/in	DWG NO.: X-X1511H-XX-N0
APPD	DATE	SIZE: A4	WEIGHT SHEET REVISION 1.0g 1/1 A0
XKB INDUSTRIAL PRECISION CO.,LIMITED			

广东星坤科技股份有限公司  
文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX				ANGLAR ±5°
ΔX				≤4 ±0.2
ΔX				4<L≤16 ±0.3
MARK				16<L≤63 ±0.4
				L>63 ±0.5