




Specifications:  
 规格:  
 Voltage rating: 250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating: 3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage: 800V AC/minute  
 耐受电压: 800V AC/分钟  
 Temperature range: -25°C~+85°C  
 温度范围: -25°C~+85°C  
 Insulation resistance: 1000MΩ min  
 绝缘电阻: 1000MΩ Min  
 Contact resistance: 20mΩ Max  
 接触电阻: 20mΩ Max

X2000 W R S - XX - 6T SN  
 ① ② ③ ④ ⑤ ⑥ ⑦


1. Series No
2. Category: W-Wafer
3. Welding Board Angle: R-Stright 90°
4. Weding Way: S-SMT
5. Row No. Pin No: XX-02~15P
6. Material: 6T-PA6T UL94V-0 Beige
7. Plating: SN-Tin Plated



Schematic Diagram of 10, 11, 12, 13, 14, 15-Hole



PCB LAYOUT



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	8.00	4.55	09	16.00	22.00	18.55
03	4.00	10.00	6.55	10	18.00	24.00	20.55
04	6.00	12.00	8.55	11	20.00	26.00	22.55
05	8.00	14.00	10.55	12	22.00	28.00	24.55
06	10.00	16.00	12.55	13	24.00	30.00	26.55
07	12.00	18.00	14.55	14	26.00	32.00	28.55
08	14.00	20.00	16.55	15	28.00	34.00	30.55

X2000WRS-XX-6TSN	PA6T	Brass	X2000H
PART NO	Material	Material(Pin)	Suitable XKB Housing

广东星坤科技股份有限公司

生	日期
效	日期
MARK	DESCRIPTION

REVISIONS	DATE	REVISED	APPROVED
ANGLAR		±5°	
L ≤ 4		±0.2	
4 < L ≤ 16		±0.3	
16 < L ≤ 63		±0.4	
L > 63		±0.5	
UNSPECIFIED TOLERANCES			



DSND	SCALE: N/A	MODEL TYPE: 2.0mm Crimp Style Connector
DWN	VIEW:	PART NO.: X2000WRS-XX-6TSN
CHKD	UNIT: mm/in	DWG NO.: X-X2000WRS-XX-6TSN
APPD	SIZE: A4	

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

文件工程章