




XKB Connectivity

■ 规格 Specifications:

- 额定电压 Votage rating:250V AC/DC
- 额定电流 Current rating:3A AC/DC
- 耐电压 Withstanding voltage:1500V AC/minute
- 温度区间 Temperature range:-40℃~+105℃
- 绝缘电阻 Insulation resistance:≥500MΩ
- 接触电阻 Contact resistance:≤10mΩ
- 环境测试后 After environmental testing:≤20mΩ

XKB Connectivity
X2521 T F- P SN-G
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: T-Terminal
- ③ Welding Board Angle: F-Female
- ④ Material: P-Phosphor Bronze
- ⑤ Plating style: SN-Bright tin plating
- ⑥ G:matin9 -G



XKB Connectivity

X2521 TF-PSN-G	PhosPhor Bronze	AWG#22-28	1.80mm(MAX)	Tin-Plated	X2521HM-G
PART NO	Material	Wire Ran9e	Insultion O.D	Finsh(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 效 日期

文件工程章

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
					L ≤ 4	±0.2
					4 < L ≤ 16	±0.3
					16 < L ≤ 63	±0.4
					L > 63	±0.5
UNSPECIFIED TOLERANCES						

DSND	DATE	SCALE: N/A	MODEL TYPE: X2521TF-PSN-G
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0