



Specifications:
 规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating:10A AC/DC
 额定电流: 10A AC/DC
 Withstanding voltage:1500V AC/minute
 耐受电压: 1500V AC/分钟
 Temperature range:-25°C~+85°C
 温度范围: -25°C~+85°C
 Insulation resistance:1000MΩ min
 绝缘电阻: 1000MΩ Min
 Contact resistance:10mΩ Max
 接触电阻: 10mΩ Max

X5050 W R - 04 B - 4T SN
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.Row No.Pin No:04Pin
- 5.Special No:B-With Buckle the poi sitive angle
- 6.Material:4T-Nylon 4T UL94V-0 ;
9T-Nylon 9T UL94V-0; N2-Nylon 66 UL94V-2
- 7.Plating:SN-Bright Tin Plated

Recommended PCB
 Layout ±0.05

X5050WR-XXB-N2SN	Nylon 66 UL 94V-2	Brass (Tin Plated)	Stainless Steel(Tin Plated)	X5050H
X5050WR-XXB-9TSN	Nylon 9T UL 94V-0			
X5050WR-XXB-4TSN	Nylon 4T UL 94V-0			
PART NO	Material	Material(Pin)	Material(MetalBand)	Suitable XKB Housing

广东星坤科技股份有限公司

ΔX	日期
ΔX	
ΔX	
MARK	DESCRIPTION

文件工程章

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5
UNSPECIFIED TOLERANCES	



DSND	SCALE: N/A	MODEL TYPE: 5.08mm Crimp Style Connector
DWN	VIEW:	PART NO.: X5050WR- 04B-4TSN
CHKD	UNIT: mm/in	DWG NO.: X-X5050WR- 04B-4TSN
APPD	SIZE: A4	WEIGHT
XKB INDUSTRIAL PRECISION CO.,LIMITED		SHEET
		REVISION
		1/1
		A0