


Recommended P.C.B Layout
General Tolerance±0.05



Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 7A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X9396 WR-XX A-NO SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Stright 90°
- ④ Row No.Pin No.XX-02-15
- ⑤ Special No.A-There are graps
- ⑥ Material:N0-Nylon66 UL94V-0
- ⑦ Planting Category:SN-Bright tin plating

| Poles | Dimensions(mm) | | Poles | Dimensions(mm) | |
|-------|----------------|-------|-------|----------------|-------|
| | A | B | | A | B |
| 02 | 3.96 | 7.92 | 09 | 31.68 | 35.64 |
| 03 | 7.92 | 11.88 | 10 | 35.64 | 39.60 |
| 04 | 11.88 | 15.84 | 11 | 39.60 | 43.56 |
| 05 | 15.84 | 19.80 | 12 | 43.56 | 47.52 |
| 06 | 19.80 | 23.76 | 13 | 47.52 | 51.48 |
| 07 | 23.76 | 27.72 | 14 | 51.48 | 55.44 |
| 08 | 27.72 | 31.68 | 15 | 55.44 | 59.40 |

| | | | | |
|------------------|-------------------|---------------|-------------|-------------------------|
| X9396WR-XXA-N0SN | Nylon 66 UL 94V-0 | Brass | Tin-Plated | X9396H |
| PART NO | Material | Material(Pin) | Finish(Pin) | Suitable X K B Terminal |

| | | | | | |
|--------------------------------------|------|-------------|--|-------|----------|
| DSND | DATE | SCALE: N/A | MODEL TYPE: X9396WR-XXA-N0SN | | |
| DWN | DATE | VIEW: | PART NO.: 3.96mm Crimp Style Connectors | | |
| CHKD | DATE | UNIT: mm/in | DWG NO.: X9396WR-XXA-N0SN | | |
| APPD | DATE | SIZE: A4 | WEIGHT | SHEET | REVISION |
| XKB INDUSTRIAL PRECISION CO.,LIMITED | | | 1.0g | 1/1 | A0 |

广东星坤科技股份有限公司

| | |
|------|-------------|
| ΔX | 日期 |
| ΔX | 日期 |
| ΔX | 日期 |
| MARK | DESCRIPTION |

文件工程章

REVISIONS
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

UNSPECIFIED TOLERANCES

| | |
|---------|------|
| ANGLAR | ±5° |
| L≤4 | ±0.2 |
| 4<L≤16 | ±0.3 |
| 16<L≤63 | ±0.4 |
| L>63 | ±0.5 |