



Specifications:

规格:

- Voltage rating:600V AC/DC
- 额定电压: 600V AC/DC
- Current rating:19A AC/DC
- 额定电流: 19A AC/DC
- Withstanding voltage:5000V AC/minute
- 耐受电压: 5000V AC/分钟
- Temperature range:-40°C-+105°C
- 温度范围: -40°C-+105°C
- Insulation resistance:1000MΩ min
- 绝缘电阻: 1000MΩ Min
- Contact resistance:3.5mΩ Max
- 接触电阻: 3.5mΩ Max

X9635 H M - XX - N2
 ① ② ③ ④ ⑤

- 1.Series No
- 2.Category:H-HSG
- 3.Category:M-Male Housing
- 4.Row No.Pin No:XX-02~10P
- 5.Material:N0-Nylon 66 UL94V-0 ;
N2-Nylon 66 UL94V-2 (White)

Poles	Dimensions(mm)	
	A	B
2	13.97	6.35
3	20.32	12.70
4	26.67	19.05
5	33.02	25.40
6	39.37	31.75
8	52.07	44.45
10	64.77	57.15

X9635HM-XX-N0	Nylon 66 UL94V-0	X9635W	X9635TF
X9635HM-XX-N2	Nylon 66 UL94V-2		
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						



XKB INDUSTRIAL PRECISION CO., LIMITED

DSND	SCALE: N/A	MODEL TYPE: 6.35mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9635HM-XX-N2
CHKD	UNIT: mm/in	DWG NO.: X-X9635HM-XX-N2
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0