

Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:1A AC/DC

额定电流: 1A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25°C~+85°C

温度范围: -25°C~+85°C

Insulation resistance: 500MΩ min


绝缘电阻: 500MΩ Min

Contact resistance:30mΩ Max



接触电阻: 30mΩ Max

X9862 W R S -XX A -6T SN
① ② ③ ④ ⑤ ⑥ ⑦ ⑧


1. Series No
2. Category :W-Wafer
3. Welding Board Angle:R-Straight 90°
4. Welding Way:S-SMT
5. Row No.Pin No:XX-02P-30P
6. Special No: A-With Lock
7. Material: 6T-Nylon 6T
8. Plating: Tin Plating




04P~30P




02P



03P



P-C-B LAYOUT



Poles	Dimensions(mm)	
	A	B
02	1.25	7.45
03	2.50	8.70
04	3.75	9.95
05	5.00	11.20
06	6.25	12.45
07	7.50	13.70
08	8.75	14.95
09	10.00	16.20
10	11.25	17.45
11	12.50	18.70
12	13.75	19.95
13	15.00	21.20
14	16.25	22.45
15	17.50	23.70
20	23.75	29.95
21	25.00	31.20
25	30.00	36.20
30	36.25	42.45

X9862WRS-XXA-6TSN	Nylon 6T	Brass	X9862H-A
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND	SCALE: N/A	MODEL TYPE: 1.25mm Crimp Style Connector
DWN	VIEW:	PART NO.: X9862WRS-XXA-6TSN
CHKD	UNIT: mm/in	DWG NO.: X-X9862WRS-XXA-6TSN
APPD	SIZE: A4	

广东星坤科技股份有限公司

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGLAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
					16 < L ≤ 63 ±0.4
					L > 63 ±0.5



XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0

文件工程章