



XJB Connectivity


Pin数	尺寸A	尺寸B
1		2
2	2	4
3	4	6
4	6	8
5	8	10
6	10	12
7	12	14
8	14	16
9	16	18
10	18	20
11	20	22
12	22	24
13	24	26
14	26	28
15	28	30
16	30	32
17	32	34
18	34	36
19	36	38
20	38	40
21	40	42
22	42	44
23	44	46
24	46	48
25	48	50
26	50	52
27	52	54
28	54	56
29	56	58
30	58	60
31	60	62
32	62	64
33	64	66
34	66	68
35	68	70
36	70	72
37	72	74
38	74	76
39	76	78
40	78	80




TYPE 1




TYPE 2




XJB Connectivity
PCB LAYOUT



TYPE 1



TYPE 2



XJB Connectivity

规格 Specifications:

- 额定电压 Voltage rating:250VAC/DC.
- 额定电流 Current rating:3A AC/DC
- 耐电压 Withstanding voltage:1000V AC/minute
- 温度区间 Temperature range:-40℃to+105℃
- 绝缘电阻 Insulation resistance:≥1000MΩ Min
- 接触电阻 Contact resistance:≤20MΩ Max
- 材料 Material: PA6T 94V-0
- 镀层 Plating Category: 1U"Gold
- 颜色 color: Blank-Natural color

XJB Connectivity

X4612 WVS - XXI - C40 D44 - X

(01) (02) (03) (04) (05) (06) (07) (08) (09)

- (01) Series No.
- (02) Category:W-wafer
- (03) Welding Board Angle:V-Stright 90°
- (04) Welding Way:S-SMT
- (05) Row No-Pin No:XX-01P-40P
- (06) Plastic height: l=2.0mm
- (07) Pin length:C=3.0mm
- (08) Pin length:D=6.0mm
- (09) TYPE:R1;R2

XJB Connectivity

PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XJB Terminal
X4612WVS-XXI-C40D44-X	PA6T 94V-0	Brass	1U"Gold	X4612F

广东星坤科技股份有限公司

生
發

日
期

文件工程章

REVISIONS

www.xkpcb.com www.hellixkb.com

UNSPECIFIED TOLERANCES

www.hellixkb.com

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X4612WVS-XXI-C40D44-X
CHKD	DATE	UNIT: mm/in	PART NO.: 2.00mm Crimp Style Connector
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0