



Recommended P. C. B
Layout(±0.05)

Technical Date
 Pin(outer sleeve):Brass,machined CuZn38pb2
 Clip (Contact 4 Finger):Beryllium copper,heat treated
 Insulator:PBT UL94V-0 colour:black
 Gold Plated:2um"/80u"Ni,GF
 Current rating:3Amps
 Mechanical Life:min 500 cycles
 Contact resistance: 10mΩ max
 Dielectric strength:1000V
 Operating temperature:-40 °C to +105°C
 Soldering temperature:+255°C

X5621 F V -2xXX- C762 D1150 -1150
 ① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No-Pin No:2xXX-2x01Pin-2xXXPin
- 5.line spacing:C=7.62mm
- 6.Pin Length:D=11.50mm
- 7.1150:Type1150

X5621FV-2xXX-C762D1150-1150	PBT	Brass	X5621W
PART NO	Material	Material(Pin)	Suitable XKB Wafer

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
				ANGULAR ±5°
				L ≤ 4 ±0.2
				4 < L ≤ 16 ±0.3
				16 < L ≤ 63 ±0.4
				L > 63 ±0.5



DSND	SCALE: N/A	MODEL TYPE: 2.54mm BTB Style Connector
DWN	VIEW:	PART NO.: X5621FV-2xXX-C762D1150-1150
CHKD	UNIT: mm/in	DWG NO.:
APPD	SIZE: A4	X-X5621FV-2xXX-C762D1150-1150
XKB INDUSTRIAL PRECISION CO.,LIMITED		WEIGHT SHEET REVISION 1/1 A0