


Recommended PCB Layout  
PCB Board Tolerance±0.05



Specifications:

规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:3A AC/DC  
额定电流: 3A AC/DC  
Withstanding voltage:500V AC/minute  
耐受电压: 500V AC/分钟  
Temperature range:-40℃~+105℃  
温度范围: -40℃~+105℃  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance:≤20mΩ  
接触电阻: ≤20mΩ  
After environmental testing:≤30mΩ  
环境测试后: ≤30兆欧

X9555W V - 2xXX-6T V01

① ② ③ ④ ⑤ ⑥

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:V-Straight 180°
- 4.Row No-Pin No:2xXX-2x02P~2x32P
- 5.Material:6T:PA6T 94V-0
- 6.Plating Category: V01-All Gold Flash

poles	Dimensions(mm)		poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B		A	B
2x02	2.54	12.68	2x11	25.40	35.71	2x20	48.26	58.40
2x03	5.08	15.22	2x12	27.94	38.25	2x22	53.34	63.48
2x04	7.62	17.76	2x13	30.50	40.65	2x24	58.42	68.56
2x05	10.16	20.30	2x14	33.04	43.19	2x25	60.86	71.10
2x06	12.70	22.84	2x15	35.56	45.80	2x27	65.94	76.18
2x07	15.24	25.38	2x16	38.10	48.34	2x28	68.48	78.72
2x09	17.78	27.92	2x17	40.64	50.78	2x29	71.02	81.26
2x08	20.32	30.46	2x18	43.18	53.32	2x30	73.70	84.15
2x10	22.86	33.00	2x19	45.72	56.26	2x32	78.74	89.00

X9555WV-2xXX-6TV01	PA6T 94V-0	Brass	Gold-Flash	X9555H
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期					units: mm
ΔX						tolerance: X.X ±0.2mm
ΔX						X.XX ±0.1mm
ΔX						X.XXX ±0.05mm
MARK	DESCRIPTION	DATE	REVISED	APPROVED		UNSPECIFIED TOLERANCES
文件工程章						

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector	
DWN		DATE		VIEW:	PART NO.: 2.54mm Crimp Style Connectors	
CHKD		DATE		UNIT: mm/in	DWG NO.: X9555WV-2xXX-6TV01	
APPD		DATE		SIZE: A4		
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0