

Hyper-miniature Slide Switchess



RoHS Compliant


Features -

- High Contact Reliability
 Twin-contact clip mechanism for high contact reliability.
- 2. Gold-plated contacts suitable for low current applications
- 3. For PC board mounting
- 4. Improved operability

The independent detent structure provides a light operating touch.


Specifications

Datin	0.4VA AC/DC	Voltagr range	20mV~48V	
		Current range	1 μ A~50mA	
Rating	Max.	50mA 40V AC/DC		
	Min.	1μA 20mV AC/[OC	
Initial contact resistance		50mΩ max.	$(1.5\text{mA}~200\mu\text{VAC})$	
Dielectric strength		250VAC 1 minute		
Initial insula	ation resistance	500MΩ min.	(250VDC)	
Electrica	Llifo	10,000 cycles at max. rating.		
Electrica	ııııe	50,000 cycles at min. rating or 0.4VA		
Operating force		0.69~4.9N		
Operating temperature range		_20°C~+85°C		
Storage temperature range		-40°C~+85°C		



SPDT






Switching function	Viewed from part No. marking side		
Part No.	_		
AS1D-2M-10-Z	ON	_	ON
☆AS1E-2M-10-Z	ON	OFF	ON
Connecting terminals	2-1	_	2-3

DPDT

Distance between two terminal rows: 2.54 mm






Switching function	Viewed from part No. marking side		
Part No.			
AS2D-2M-10-Z	ON	_	ON
★AS2E-2M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6

DPDT

Distance between two terminal rows: 5.08 mm






Switching function	Viewed from	m part No. m	arking side
Part No.			
★AS2N-2M-10-Z	ON	_	ON
★AS2P-2M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6

SPDT

 ${\it *Mounting height: 3.1mm}$






Switching function	Viewed from part No. marking side		
Part No.			
AS1D-5M-10-Z	ON	_	ON
AS1E-5M-10-Z	ON	OFF	ON
接続端子 Connecting terminals	2-1	_	2-3

DPDT

*Mounting height : 3.1mm






Switching function	Viewed from	m part No. m	arking side
Part No.			_
AS2D-5M-10-Z	ON	_	ON
★AS2E-5M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6

DPDT


*Mounting height: 5.15mm






Switching function	Viewed from	m part No. m	arking side
Part No.			
★AS2N-5M-10-Z	ON	_	ON
★AS2P-5M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6








Switching function	Viewed from part No. marking side		
Part No.			
AS1D-6M-10-Z	ON	_	ON
★AS1E-6M-10-Z	ON	OFF	ON
Connecting terminals	2-1	_	2-3

DPDT

*Mounting height: 3.1mm




Switching function	Viewed from part No. marking side		
Part No.			
☆AS2D-6M-10-Z	ON	_	ON
★AS2E-6M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6

DPDT


*Mounting height: 5.15mm






Switching function	Viewed from	m part No. m	arking side
Part No.			
☆AS2N-6M-10-Z	ON	_	ON
★AS2P-6M-10-Z	ON	OFF	ON
Connecting terminals	2-1 5-4	_	2-3 5-6

■ Actuator Shape



■Bracket Installation Procedure



■ Optional Accessories 《Sold separately》

Part Name	Bracket
Part No.	140000640324
Dimensions	9.55

■PC Hole Layouts

Series	P/C te	rminal	Right Angle terminal	
	Whithout bracket	Whit bracket	0.2inch pitch	0.3inch pitch
AS1D AS1E	$ \begin{array}{c c} 3 \cdot \phi 1 \\ \hline 2.54 & 2.54 \end{array} $	2.54 2.54 2.54 2.54	5.08 5.08	5-φ1
AS2D AS2E	2.54 2.54 6-\phi1	254 254 254 254 8·\$1	8-\phi 1	8 \phi 1
AS2N AS2P	2.54 2.54	254 254 254 254 8-61	5.08 2.54	7.62 2.54