

PRODUCT-DETAILS

GS201 AC-C25/0.03

GS201 AC-C25/0.03 Residual Current Circuit Breaker with Overcurrent Protection



General Information

Extended Product Type	GS201 AC-C25/0.03
Product ID	2TAZ210111R2254
EAN	6940342287117
Catalog Description	GS201 AC-C25/0.03 Residual Current Circuit Breaker with Overcurrent Protection
Long Description	Residual Current Circuit Breaker with Overcurrent Protection GS201 AC-C25/0.03

Technical

Standards	IEC 61009 GB 16917
Tripping Characteristic	C
Type of Residual Current	AC type
Rated Operational Voltage	230 V AC
Rated Current (I_n)	25 A
Rated Residual Current	30 mA
Rated Short-Circuit Capacity (I_{cn})	6 kA
Maximum Breaking Capacity	6 kA
Number of Poles	1+N
Number of Protected Poles	1
Number of Earth Leakage Circuit Breakers	1

(ELCBs)

Operating Characteristic	Instantaneous
Position of Neutral Terminals	Right
Release Type	C
Accessories Available	Yes

Technical UL/CSA

Short-Circuit Current Rating (SCCR)	30 mA
-------------------------------------	-------

Dimensions

Product Net Width	69 mm
Product Net Height	0.085 m
Product Net Depth / Length	70 mm
Product Net Weight	0.203 kg

Container Information

Package Level 1 EAN	6940342287117
---------------------	---------------

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363010
Country of Origin	China (CN)

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	No declaration needed
Instructions and Manuals	No document needed

Popular Downloads

Data Sheet, Technical Information	1SXF400005C2013
Instructions and Manuals	No document needed

Classifications

ETIM 7	EC002281 - Distributor assembly with combination RCCB/MCB
ETIM 8	EC002281 - Distributor assembly with combination RCCB/MCB
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Consumer
CN8	85363010

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Circuit Breakers with Overcurrent Protection RCBO

