





手柄尺寸		
F	K	Y
1.5*1.5	1.6	3.6
2.0*2.0	2.1	4.0



P O B MOUNTING PATTERN DIMENSION
The following soldering are recommended for soldering



Specification

Part Name	Material	Specification
Operating Life	10,000	Cover plate silver plating of stainless steel
Contact rating	300mA@4V DC.	button black PA46/9T
Insulation resistance	>10Ω	spring ecru Stainless steel wire
Contact resistance	≤100MΩ	reed silver Phosphor bronze plated with silver
Dielectric Strength	250 V 50HZ 1Min	base black PA46/9T/LCP
Travel	0.2±0.1mm	terminal silver Phosphor copper plating silver

Mechanical

P/N	Operation Force(gf)	Height mm	Hook	Leads Spacing (mm)	Ground Pin	Pins Position
YSS-0	2	200±70	A 2	1.5±0.15	T	0
			B 3			
			C 4			

X.	X.°	UNITS
±0.50	± 2°	mm
±0.30	± 1°	
±0.10	± 0.5°	
XXX ± 0.05		

PART NO. YSS-0	TITLE: 大六立式三脚拨动开关
APPD: RODGER	DWG NO: YSS-0
CHKD: RDC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/09/21	

yi yuwan 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

FINISH	Q'TY
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD. AND SHOULD BE REPRODUCED AND SHOWN TO ANY OTHER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD.	