






RoHS

CAD GENERATED DRAWING. DON'T CHANGE BY HAND.

REV.	ECN. NO.	APPD.



PCB Layout(Pattern side)



Specification

Operating Life	10,000
Contact rating	300mA@4V DC.
Insulation resistance	>100Ω
Contact resistance	≤100MΩ
Dielectric Strength	250 V 50HZ 1Min
Travel	0.2±0.1mm

⑤	Terminal	3	Brass	Silver	
①	Contact reed	1	Beryllium copper	silver covered	
②	Handle	1	PA46	Black	
③	Cover	1	SUS	Natural	
④	Base	1	PA46	Black	
No	Name	Number	Qty	Material	Remarks

P/N	Operating Force(gf)	Height mm	Lead shape (G,J,T)	Ground pin (0,1)	Pegs (0,1)
YSS-R	3	230±80	C	4	T
			B	3	
			A	2	

Mechanical

X. ±0.50	X.° ±2°	UNITS mm
.X ±0.30	.X° ±1°	
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		FINISH
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD		Q'TY



深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO. YSS-R	TITLE: 大六脚插2+1拨动开关
APPD: ROGER	DWG NO.: YSS-R
CHKD: ROC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	