





P. C. B MOUNTING PATTERN DIMENSION

the following soldering are recommended for reflow soldering



CIRCUIT DIAGRAM



Specification

Operating Life	10,000	Part Name	Material	Specification
Contact rating	300mA@4V DC.	Cover plate	silver white	Silver plating of stainless steel
Insulation resistance	>100Ω	button	black	PA46/9T
Contact resistance	≤100W	spring	ecru	Stainless steel wire
Dielectric Strength	250 V 50HZ 1Min	reed	silver	Phosphor bronze plated with silver
Travel	0.2±0.1mm	base	black	PA46/9T/LCP
		terminal	silver	Phosphor copper plating silver

Mechanical

P/N	Operating Force(gf)	Height mm	Leads Shape (G,J,T)	Ground pin (0,1)	Pegs Option (0,1)		
YSS-T	2	200±70	C	4	T	0	0
			B	3			
			A	2			

X. ±0.50	X.° ±2°	UNITS mm
.X ±0.30	.X° ±1°	
.XX ±0.10	.XX° ±0.5°	MAT'L
.XXX ±0.05		FINISH
		Q'TY

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF YIYUAN TECHNOLOGY CO.,LTD AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF YIYUAN TECHNOLOGY CO.,LTD

yi YUAN 深圳市怡远科技有限公司
SHENZHEN YIYUAN TECHNOLOGY CO.,LTD

PART NO. YSS-T	TITLE: 大端轴连接
-------------------	-----------------

APPD: ROGER	DWG NO.: YSS-T
CHKD: ROC	SCALE SHEET REV. 1/1 1/1 A1
DR: BILLY WANG 2020/08/21	