

1 2 3 4 5 6 7 8 9 10

ROHS

12.00

12.02


15.00

7.10

20.00

7.98

4.50



MAPX

MODIFICATION

DRW

DATE

- NOTES:
SPECIFICATION:
1. CURRENT RATING: 3.0A MAX
2. VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 °C ~ 85 °C

NO.	DESCRIPTION	MATERIAL	REMARKS	QTY
7	SHELL	塑料 (改性塑料)	BLACK (可订制)	1PCS
6	SHELL	SPCC	NI Plated	1PCS
5	CONTACT	POB (镀银磷铜包铜)	Au20"	1SET
4	HOUSING	PBT	BLACK	1PCS
3	SHELL	STAINLESS STEEL	NI Plated	1PCS
2	CONTACT	COPPER ALLOY	Au/Ni Plated	1SET
1	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK	1PCS

产品图
PRODUCT CHART DWG

公差一览表
TOLERANCE UNLESS OTHERWISE

公差	公差	公差	公差	公差
X	±0.25	X	±5°	
X	±0.20	X	±2°	
XX	±0.05	XX	±1°	
XXX	±0.02	XXX	±0.5°	

单位: MM
比例: 1:1
日期: 2020-05-22
制图: YANG
审核: 郭裕富
核准: 黄国荣
制图料号: 917-B88C201AH70206
产品名称: 转接头
转接头-0.5英寸转0.120英寸母头-黑色

深圳市精拓金电子有限公司
Shenzhen Jing Tuo Jin Electronics Co., Ltd.

角法: 第三角
版本: AD