



MATING HEIGHT	PLUG	SOCKET
4.0	1.0	3.0
4.5	1.0	3.5
5.0	1.0	4.0
5.5	1.0	4.5
6.0	2.0	4.0
6.5	2.0	4.5



No. of contacts	Dimensions					No. of contacts	Dimensions				
	A	B	C	D	E		A	B	C	D	E
4	3.50	0.80	1.80	2.60	4.00	54	23.50	20.80	21.80	22.60	8
6	4.30	1.60	2.60	3.40		56	24.30	21.60	22.60	23.40	
8	5.10	2.40	3.40	4.20		58	25.10	22.40	23.40	24.20	
10	5.90	3.20	4.20	5.00		60	25.90	23.20	24.20	25.00	
12	6.70	4.00	5.00	5.80		62	26.70	24.00	25.00	25.80	
14	7.50	4.80	5.80	6.60		64	27.50	24.80	25.80	26.60	
16	8.30	5.60	6.60	7.40		66	28.30	25.60	26.60	27.40	
18	9.10	6.40	7.40	8.20		68	29.10	26.40	27.40	28.20	
20	9.90	7.20	8.20	9.00		70	29.90	27.20	28.20	29.00	
22	10.70	8.00	9.00	9.80		72	30.70	28.00	29.00	29.80	
24	11.50	8.80	9.80	10.60		74	31.50	28.80	29.80	30.60	
26	12.30	9.60	10.60	11.40		76	32.30	29.60	30.60	31.40	
28	13.10	10.40	11.40	12.20	78	33.10	30.40	31.40	32.20		
30	13.90	11.20	12.20	13.00	80	33.90	31.20	32.20	33.00		
32	14.70	12.00	13.00	13.80	82	34.70	32.00	33.00	33.80		
34	15.50	12.80	13.80	14.60	84	35.50	32.80	33.80	34.60		
36	16.30	13.60	14.60	15.40	86	36.30	33.60	34.60	35.40		
38	17.10	14.40	15.40	16.20	88	37.10	34.40	35.40	36.20		
40	17.90	15.20	16.20	17.00	90	37.90	35.20	36.20	37.00		
42	18.70	16.00	17.00	17.80	92	38.70	36.00	37.00	37.80		
44	19.50	16.80	17.80	18.60	94	39.50	36.80	37.80	38.60		
46	20.30	17.60	18.60	19.40	96	40.30	37.60	38.60	39.40		
48	21.10	18.40	19.40	20.20	98	41.10	38.40	39.40	40.20		
50	21.90	19.20	20.20	21.00	100	41.90	39.20	40.20	41.00		

Specifications:  
 规格:  
 Voltage rating:200V AC/DC  
 额定电压: 200V AC/DC  
 Current rating:1A AC/DC  
 额定电流: 1A AC/DC  
 Withstanding voltage:500V AC/minute  
 耐受电压: 500V AC/ 分钟  
 Temperature range:-40 -+105  
 温度范围: -40 -+105  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance:≤20mΩ  
 接触电阻: ≤20mΩ  
 After environmental testing:≤40mΩ  
 环境测试后: ≤40兆欧

X0812 W V S-XX X S- 9T V01  
 1. Series No  
 2. Category:W-WAFER  
 3. Welding Board Angle:V-Straight 180°  
 4. Welding Way:S-SMT  
 5. Row No-Pin No:XX-04P-100P  
 6. Height:A=1.0mm;B=2.0mm  
 7. Special No:S-With positioning Column  
 8. Material:9T-PA9T UL94V-0 Black  
 9. Plating:V01-Gold Flash

广东星坤科技股份有限公司

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ANGLAR				±5°
L ≤ 4				±0.2
4 < L ≤ 16				±0.3
16 < L ≤ 63				±0.4
L > 63				±0.5

DSND  
 DWN  
 CHKD  
 APPD

SCALE: N/A  
 VIEW:  
 UNIT: mm/in  
 SIZE: A4

**XKLB**

XKB INDUSTRIAL PRECISION CO., LIMITED

MODEL TYPE: 0.8mm BTB Style connector	WEIGHT	SHEET	REVISION
PART NO.: X0812WVS-XXS-9TV01		1/1	A0
DWG NO.: X-X0812WVS-XXS-9TV01			