



REV.	ECN. NO.	APPD.
A		

NOTES:  
 Current Rating:2.0AMP  
 Contact Resistance:20mΩ max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ min  
 Operation Temperature:-40°C to +105°C

Contact Material:Phosphor Bronze  
 Contact plating:Au or Sn Over Ni  
 Insulator Material:PA6T+30%GF(UL94V-0)  
 Contact plated:Gold Flash





Recommended P.C.B Layout(TOP Side)  
 (PCB BOARD TOLERANCE±0.05)



### Ordering Information

MTF243-2XX M U X

No. of Pins per ROW:02-40PIN  
 Series No.  
 1=TYPE 1  
 2=TYPE 2



X. ± 0.30	X.° ± 5°	UNITS mm	NAME(INTENDED USE)	MINTRON CO.,LTD.
.X ± 0.20	.X° ± 2°	MAT'L	PART NO.(INTENDED USE)	
.XX ± 0.10	.XX° ± 1°	FINISH	APPD: SUNNY	
.XXX ± 0.05	.XXX° ± 0.5°		CHKD: LISA	
FEMALE HEADER CONNECTOR		Q'TY	DR: ZOE 2006-11-28	
			TITLE: 2.00 FEMALE HEADER DUAL SMT H=4.3 W=4.0	
			DWG NO.: MTF243-2XXMUX	
			SCALE 1/1	
			SHEET 1/1	
			REV. A	