



LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		A		RELEASED	17DEC2009	J.C	K.O
		AI		ECR-10-007032	31MAR2010	J.C	A.G





2050723-1 AS SHOWN





SECTION A-A
SCALE 4:1

NOTES

- ① LEVER ASSEMBLED IN PRE-LOCKED POSITION. LEVER MUST BE LOCKED BEHIND THE DIMPLE.
- 2 PACKAGING: LOOSE PIECE IN BOX.
- ③ TOLERANCES UNLESS OTHERWISE SPECIFIED ACC. TO DIN 16901-120



① ②



1-2050723-4	964826-1	PBT-GF20	VIOLET	4006	A, C, E, I, II	LEVER	1	2
	1-2050724-4	PBT-GF20	GREY	7036		COVER	1	1
1-2050723-3	964826-1	PBT-GF20	VIOLET	4006	D, B, E, II	LEVER	1	2
	1-2050724-3	PBT-GF20	BLACK	9011		COVER	1	1
2050723-5	964826-1	PBT-GF20	VIOLET	4006	A, B, E	LEVER	1	2
	2050724-5	PBT-GF20	BROWN	1011		COVER	1	1
2050723-4	964826-1	PBT-GF20	VIOLET	4006	A, C, E	LEVER	1	2
	2050724-4	PBT-GF20	GREY	7036		COVER	1	1
2050723-3	964826-1	PBT-GF20	VIOLET	4006	D, B, E	LEVER	1	2
	2050724-3	PBT-GF20	BLACK	9011		COVER	1	1
2050723-2	964826-1	PBT-GF20	VIOLET	4006	C, D	LEVER	1	2
	2050724-2	PBT-GF20	BLUE	5012		COVER	1	1
2050723-1	964826-1	PBT-GF20	VIOLET	4006	A, F	LEVER	1	2
	2050724-1	PBT-GF20	GREEN	6018		COVER	1	1
TE-ASSY-NO	TE-PART NO	MATERIAL	COLOUR	RAV	CODING	DESCRIPTION	QTY.	ITEM NO

<small>THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION. BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.</small>		DWN: J. CHEN 17DEC2009 CBY: A. GUANCO 17DEC2009 APVD: K. QIA 17DEC2009		Tyco Electronics Shanghai, CHINA	
DIMENSIONS mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: ③		NAME: COVER, ASSY, MOS-HSG., 2x16 POS. PRODUCT SPEC: 108-18924 APPLICATION SPEC: 114-18630	
MATERIAL: SEE TABLE		FINISH:		SIZE: A2 CAGE CODE: 200779 DRAWING NO: 2050723	
CUSTOMER DRAWING		WEIGHT:		RESTRICTED:	